



Distance Rod for ID14 and IDS108

Ø20mm x 1400mm



Content



Weight: 1.4 kg / 3.1 lb




nexo-sa.com

ZA du Pre de la Dame Jeanne
60128 PLAILLY - France

- Read this document before using.
- Keep this document.
- Observe all warnings and cautions.



Dimensions:




Placement of the wire:

We recommend using a cable with $2 \times 0.75 \text{ mm}^2$ (AWG18) section, length 2.3m (7.5 feet)

Feed the cable through the openings in the distance rod.

Then cable the SpeakON (2+/2-).



Assembly:

Screw adapters M10 on the Sub and on ID14 by hand without tools.	Place distance rod, tighten the two clamping knobs
<p>Diagram showing the installation of screw adapters M10 on the Sub and ID14. Two circular insets show the adapters being inserted into the Sub and ID14 ports. The main diagram shows the adapters installed on the Sub and ID14 ports.</p>	<p>Diagram showing the installation of the distance rod and tightening the clamping knobs. Two circular insets show the clamping knobs being tightened. The main diagram shows the distance rod installed and the clamping knobs tightened.</p>

ENSURE THAT AUDIENCE IS NOT ALLOWED WITHIN A SAFETY AREA WICH RADIUS IS EQUAL OR HIGHER THAN ASSEMBLY HEIGHT

- NEXO cannot accept responsibility for accidents caused by any factor other than defects in this product itself.
- Please check the web site nexo-sa.com for the latest update.

NEXO

nexo-sa.com

ZA du Pre de la Dame Jeanne
60128 PLAILLY - France

- Read this document before using.
- Keep this document.
- Observe all warnings and cautions.

